

EOL Overview

Subject	J/VHV/XP/ZP/Y - Basic PDUs
EOL Original Issue Date	7 March 2017
Replacement Product	Geist Upgradeable Metered PDUs
Planned End of Sale Date	7 September 2017
Part #'s Affected	J/VHV/XP/ZP/Y series

Description

Geist is initiating an End-of-Life for all 3 phase and select single phase J/VHV/XP/ZP/Y Series PDUs with local monitoring. These product series will remain available until September 2017 or while supplies last. These products are being replaced by the new Geist Upgradeable Metered PDUs.

The Geist Upgradeable Metered PDUs support hot-swap capabilities, U-Lock outlets, and Geist's VLC technology, which enables optical data transmission from the PDU display to a handheld device, making aggregate, phase, and circuit level data available on the Geist Mobile App.

A detailed list of the affected products is provided at the end of this notice.

Geist will continue to provide existing customers with support and technical assistance on a reasonable commercial basis for a term of 3 years after final sale.

If you have any questions, concerns, or are interested in learning how the Geist Upgradeable PDUs can fill your needs, please contact your Account Manager, our Sales Desk, or visit our website at www.geistglobal.com.

Sincerely,

Geist

Warranty Information

The standard warranty remains in effect for products covered in this notice.

Contact Information

Geist
1777 Yolande Ave
Lincoln, NE 68521
Phone: 402-474-3400
watchdogsales@geistglobal.com

Please see www.geistglobal.com for complete product specifications.



Affected Models & Replacements

Model #	GU Cross	Variation
2JBAN483-102C13DTL21	None	
2JBAN483-152C13DTL21	None	
2VHVBAN488-102C13DTL21	None	
2VHVBAN488-152C13DTL21	None	
2XPBT480-103C13DTL5	None	
2XPBT480-103C13DTL6	None	
2XPBT480-153C13DTL5	None	
2XPBT480-153C13DTL6	None	
2XPRT060-103L20TL5	None	
2XPRT060-103L20TL6	None	
2XPRT060-153L20TL5	None	
2XPRT060-153L20TL6	None	
2XPRT200-103D20TL5	None	
2XPRT200-103D20TL6	None	
2XPRT200-153D20TL5	None	
2XPRT200-153D20TL6	None	
2XPRTN062-103L30TL5	None	
2XPRTN062-103L30TL6	None	
2XPRTN062-153L30TL5	None	
2XPRTN062-153L30TL6	None	
JBAN243-102D20TL21	None	
JBAN243-152D20TL21	None	
JBAN303-102IN6TL21	None	
JBAN303-152IN6TL21	None	
VHVBAN248-102C13TL21	I10059L -- MN01D4W0-42PZ68-2TL21A0A10-S	36 U-Lock C13, 6 U-Lock C19, 72in
VHVBAN248-102D20TL21	None	
VHVBAN248-152C13TL21	I10059L -- MN01D4W0-42PZ68-2TL21A0A10-S	36 U-Lock C13, 6 U-Lock C19, 72in, 10ft Cord
VHVBAN248-152D20TL21	None	
VHVBAN308-102IN6TL21	I10059L -- MN01D4W0-42PZ68-2TL21A0A10-S	36 U-Lock C13, 6 U-Lock C19, 72in



VHVBAN308-152IN6TL21	I10059L -- MN01D4W0-42PZ68-2TL21A0A10-S	36 U-Lock C13, 6 U-Lock C19, 72in, 10ft Cord
VHVBAN309-102M11TL21	I10058L -- MN01D4W0-41ML59-2TL21A0A10-S	33 U-Lock C13, 6 U-Lock C19, 2 NEMA 5-20R, 72in
VHVBAN309-152M11TL21	I10058L -- MN01D4W0-41ML59-2TL21A0A10-S	33 U-Lock C13, 6 U-Lock C19, 2 NEMA 5-20R, 72in, 10ft Cord
XPBA123-103L20TL21	None	
XPBA123-153L20TL21	None	
XPBA128-103L20TL15	None	
XPBA128-103L20TL21	None	
XPBA128-153L20TL15	None	
XPBA128-153L20TL21	None	
XPBA243-103D20TL21	I10087 -- MN01D4B1-24D203-3TL21A0A10-S	
XPBA243-153D20TL21	I10087 -- MN01D4B1-24D203-3TL21A0A10-S	10ft Cord
XPBA248-103D20TL15	None	
XPBA248-103D20TL21	None	
XPBA248-153D20TL15	None	
XPBA248-153D20TL21	None	
XPBA303-103IN6TL21	None	
XPBA303-153IN6TL21	None	
XPBA308-103IN6TL15	I10084 -- MN01D4W1-42IZ68-3TL15A0A10-S	36 C13, 6 C19, 72in
XPBA308-103IN6TL21	I10085 -- MN01D4W1-42IZ68-3TL21A0A10-S	36 C13, 6 C19, 72in
XPBA308-153IN6TL15	I10084 -- MN01D4W1-42IZ68-3TL15A0A10-S	36 C13, 6 C19, 72in, 10ft Cord
XPBA308-153IN6TL21	I10085 -- MN01D4W1-42IZ68-3TL21A0A10-S	36 C13, 6 C19, 72in, 10ft Cord
XPBT120-103L20TL6	None	
XPBT120-153L20TL6	None	
XPBT240-103D20DTL5	None	
XPBT240-103D20TL5	I10055 -- MN01D4B1-24D203-3TL5A0A10-S	
XPBT240-103D20TL6	None	
XPBT240-153D20DTL5	None	
XPBT240-153D20TL5	I10055 -- MN01D4B1-24D203-3TL5A0A10-S	10ft Cord
XPBT240-153D20TL6	None	
XPBT300-103IN6TL5	None	
XPBT300-103IN6TL6	I10082 -- MN01D4B1-36IT68-3TL6A0A10-S	30 C13, 6 C19
XPBT300-153IN6TL5	None	
XPBT300-153IN6TL6	I10082 -- MN01D4B1-36IT68-3TL6A0A10-S	30 C13, 6 C19, 10ft Cord



XPRT120-103C13TL5	None	
XPRT120-103C13TL6	I10114L -- MN01D1R1-10L138-3TL6A0H10-S	10 U-Lock 13
XPRT120-103D20TL5	I10113 -- MN01D1R1-08D203-3TL5A0H10-S	
XPRT120-103D20TL6	None	
XPRT120-153C13TL5	None	
XPRT120-153C13TL6	I10114L -- MN01D1R1-10L138-3TL6A0H10-S	10 U-Lock 13, 10ft Cord
XPRT120-153D20TL5	I10113 -- MN01D1R1-08D203-3TL5A0H10-S	10ft Cord
XPRT120-153D20TL6	None	
YBA303-103IN6PS56-IP67	I10064L -- MN01D4W1-30PN63-3PS56B0A10-S	24 U-Lock C13, 6 U-Lock C19, 72in, IP44 Plug
YBA303-103IN6TL22	I10065L -- MN01D4W1-30PN63-3TL56A0A10-S	24 U-Lock C13, 6 U-Lock C19, 72in
YBA303-153IN6PS56-IP67	I10064L -- MN01D4W1-30PN63-3PS56B0A10-S	24 U-Lock C13, 6 U-Lock C19, 72in, IP44 Plug, 10ft Cord
YBA303-153IN6TL22	I10065L -- MN01D4W1-30PN63-3TL56A0A10-S	24 U-Lock C13, 6 U-Lock C19, 72in, 10ft Cord
YBAN303-102IN6PS56-IP67	NEW	
YBAN303-102IN6TL22	I10138L -- MN01D4B0-30PN63-2TL56A0A10-S-A	24 U-Lock C13, 6 U-Lock C19, Alternating Circuits
YBAN303-152IN6PS56-IP67	NEW	
YBAN303-152IN6TL22	I10138L -- MN01D4B0-30PN63-2TL56A0A10-S-A	24 U-Lock C13, 6 U-Lock C19, Alternating Circuits, 10ft Cord
ZPBA300-106IN6PS6-IP67	I10097L -- MN01D8W1-24PH68-6PS6D0A10-S	18 U-Lock C13, 6 U-Lock C19, 72in
ZPBA300-156IN6PS6-IP67	I10097L -- MN01D8W1-24PH68-6PS6D0A10-S	18 U-Lock C13, 6 U-Lock C19, 72in, 10ft Cord
P1026 -- PXPBC300-103IN6JL6-LP	PI10002 -- MP01D4W1-42IZ68-3JL6A5A10-S	36 C13, 6 C19, 1828mm
XPBA240-103D20TL5	I10055 -- MN01D4B1-24D203-3TL5A0A10-S	
XPBA240-153D20TL5	I10055 -- MN01D4B1-24D203-3TL5A0A10-S	10ft Cord
XPBC240-103D20TL5	I10055 -- MN01D4B1-24D203-3TL5A0A10-S	
XPBC240-153D20TL5	I10055 -- MN01D4B1-24D203-3TL5A0A10-S	10ft Cord
G2240 -- EGXPBA406-103C13PS6-IP44	GI10030 -- MG01D4W1-42IZ63-3PS6B2A10-S	36 C13, 6 C19, 1828mm
G2249 -- EGXPBA426-103IZ6PS6-IP44	GI10030 -- MG01D4W1-42IZ63-3PS6B2A10-S	1828mm
G1003 -- GXPBC306-103IN6PS6-IP44	GI10035 -- MG01D4B1-36IT63-3PS6B2A10-S	30 C13, 6 C19
XPBA300-103IN6TL6	I10082 -- MN01D4B1-36IT68-3TL6A0A10-S	30 C13, 6 C19
XPBA300-153IN6TL6	I10082 -- MN01D4B1-36IT68-3TL6A0A10-S	30 C13, 6 C19, 10ft Cord
XPBC300-103IN6TL6	I10082 -- MN01D4B1-36IT68-3TL6A0A10-S	30 C13, 6 C19



XPBC300-153IN6TL6	I10082 -- MN01D4B1-36IT68-3TL6A0A10-S	30 C13, 6 C19, 10ft Cord
G2238 -- EGXPBA246-103C13PS6-IP44	GI10035 -- MG01D4B1-36IT63-3PS6B2A10-S	30 C13, 6 C19
XPRA120-103D20TL5	I10113 -- MN01D1R1-08D203-3TL5A0H10-S	8 5-20R
XPRA120-153D20TL5	I10113 -- MN01D1R1-08D203-3TL5A0H10-S	8 5-20R, 10ft Cord
XPRC120-103D20TL5	I10113 -- MN01D1R1-08D203-3TL5A0H10-S	8 5-20R
XPRC120-153D20TL5	I10113 -- MN01D1R1-08D203-3TL5A0H10-S	8 5-20R, 10ft Cord
XPRA120-103C13TL6	I10114L -- MN01D1R1-10L138-3TL6A0H10-S	10 U-Lock C13
XPRA120-153C13TL6	I10114L -- MN01D1R1-10L138-3TL6A0H10-S	10 U-Lock C13, 10ft Cord
XPRC120-103C13TL6	I10114L -- MN01D1R1-10L138-3TL6A0H10-S	10 U-Lock C13
XPRC120-153C13TL6	I10114L -- MN01D1R1-10L138-3TL6A0H10-S	10 U-Lock C13, 10ft Cord
JRAN102-102D20ST5	I10111 -- MN01D1R0-10D203-2ST5A0H10-S	
JRAN102-102D20TL5	I10112 -- MN01D1R0-10D203-2TL5A0H10-S	
JRAN102-152D20ST5	I10111 -- MN01D1R0-10D203-2ST5A0H10-S	10ft Cord
JRAN102-152D20TL5	I10112 -- MN01D1R0-10D203-2TL5A0H10-S	10ft Cord
JRCN102-102D20ST5	I10111 -- MN01D1R0-10D203-2ST5A0H10-S	
JRCN102-102D20TL5	I10112 -- MN01D1R0-10D203-2TL5A0H10-S	
JRCN102-152D20ST5	I10111 -- MN01D1R0-10D203-2ST5A0H10-S	10ft Cord
JRCN102-152D20TL5	I10112 -- MN01D1R0-10D203-2TL5A0H10-S	10ft Cord