



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugelassen. Alle Rechte vorbehalten.



HARDWIRED TERMINAL DETAIL
 (30 A, 3/PE, 200-240 V)

AGENCY COMPLIANCE:
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
 - FCC certification
 - CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:**
 1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W
 2. UNIT WEIGHT: 4 kg / 8.8 lbs
 3. SHIPPING DIMENSIONS: 2017.0 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
 4. SHIPPING WEIGHT: 6.8 kg / 15 lbs
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	6xC13, 2xC19	200-240	12/16	16
B	L2-L3	6xC13, 2xC19	200-240	12/16	16
C	L3-L1	6xC13, 2xC19	200-240	12/16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
-	-	3/PE	50/60	200-240	30	24

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
Date		Name		Bezeichnung / Description	
10/12/15		Blass		MPH2-NRV_L15-30P_18N-60_HW	
10/12/15		Votýpka		Input and Branch Metered + Outlet Metered/Switched	
-		-		Zeichnungs-Nr. / Drawing no.	
-		-		MPHR1154	
-		-		Maßstab Scale	
-		-		1:5	
-		-		Verwendet in / Used in	
-		-		Blatt/Sheet	
-		-		1/1	
Rev.	Change	Date	Name		
C	18131	31.05.2017	Petrú		