



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugelassen. Alle Rechte vorbehalten.



NEMA L21-20P  
 (20 A, 3/N/PE, 100-120/173-208 V)

**NEMA L21-20P**

**OUTPUT POWER**

BANK	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BANK
A	L1	12xNEMA 5-20	100-120	16	16
B	L2	12xNEMA 5-20	100-120	16	16
C	L3	12xNEMA 5-20	100-120	16	16

**INPUT POWER**

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	NEMA L21-20P	3/N/PE	50/60	100-120/173-208	20	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

**AGENCY COMPLIANCE:**

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)

**ENVIRONMENTAL RATING:**

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

**NOTES:**

- UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W
- UNIT WEIGHT: 4 kg / 8.8 lbs
- SHIPPING DIMENSIONS: 2017.0 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
- SHIPPING WEIGHT: 6.8 kg / 15 lbs
- (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

<p>Dimensions in mm</p>	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
Rev.	Change	Date	Name	Bezeichnung / Description	
C	18131	05.06.2017	Petrů	MPH2-NBV_L21-20P_36A Input and Branch Metered	
				Zeichnungs-Nr. / Drawing no.	Maßstab Scale
				MPHB1121	1:5
				Verwendet in / Used in	Blatt/Sheet
				-	1/1