

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.



Part #: 14240243

Model Number: C1646L

Category: Basic

Sub Category: Standard

Power Configuration: 16A, 230V, 3.6kW

Physical Configuration: 44mm x 432mm x 165 mm, Horizontal

Product Summary: C1646L - Basic Standard, 16A, 230V, 3.6kW, 1RU Horizontal, (10) Locking IEC C13, 3m power cord 2P+E (IP44), Black Powder Coat

Plug Form:



2P + E
(IP44)

Receptacle:



Locking IEC C13
(Quantity: 10)

Chassis Color Options:



Part #: 14240243

Product Specification and Options

System Features

Quantity Of Inputs	1
Voltage	220-240V
Current	16A
VA per Input (Load Capacity)	3.6kW (230V)
Frequency	50/60Hz
Over Current Protection	None
Switch	None
Power Cable Length	3m
Plug Type	IEC60309 2P + E, 16A, 250V, Splash proof IP44
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity	10
- U-Lock Color	1 circuit (Orange)
- Maximum Output per Receptacle/Socket	10A
- Voltage per Receptacle/Socket	230V
Maximum Operating Temperature	45°C/113F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U, Horizontal Rackmount
Adjustable Mount Brackets	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE, EN55032 & EN55024, IEC62368-1, RoHS
Chassis Dimensions (HxWxD)	44mm x 432mm x 165mm
Shipped Weight	4.54kg