



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.



OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	15xC13, 3xC19	200-240	12/16	16
B	L1-L2	15xC13, 3xC19	200-240	12/16	16
C	L1-L2	15xC13, 3xC19	200-240	12/16	16
D	L1-L2	15xC13, 3xC19	200-240	12/16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	NEMA L6-30P	2/PE	50/60	200-240	30	24

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

AGENCY COMPLIANCE:
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
 - FCC certification
 - CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:
 1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 52 mm (2.0") D x 107 mm (4.2") W
 2. UNIT WEIGHT: 6.7 kg / 14.7 lbs
 3. SHIPPING DIMENSIONS: 2124 mm (83.6") H x 395 mm (15.5") D x 176 mm (6.9") W
 4. SHIPPING WEIGHT: 9.5 kg / 21 lbs
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

	Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -
	-		-		-		
	Drawn	01/08/2017	Date		Name		Bezeichnung / Description
Checked	01/08/2017	Date		Name		MPH2-NBW_L6-30P_60N-120 Input and Branch Metered	
Approved	-	Date		Name		Zeichnungs-Nr. / Drawing no.	
-		-		-		MPHB 4212	
-		-		-		Verwendet in / Used in	
-		-		-		Maßstab Scale	
-		-		-		1:5	
-		-		-		Blatt/Sheet	
-		-		-		1/1	

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.