



FRONT VIEW

FOR DETAIL  
SEE DRAWING GXT5-DISPLAY




REAR VIEW



SIDE VIEW

SEE DETAIL A



DETAIL A  
SCALE 2:5

- 1 INTELLISLOT PORT
- 2 USB PORT
- 3 EXTERNAL BATTERY CAN PORTS
- 4 RS232 PORT
- 5 TERMINAL BLOCK COMMUNICATION
- 6 REPO
- 7 EXTERNAL BATTERY CONNECTOR
- 8 GROUND SCREW
- 9 15A INPUT BREAKER
- 10 INPUT POWER PLUG (5-15P, 3m/10ft)
- 11 NON PROGRAMMABLE OUTPUT RECEPTACLES (5-15R)
- 12 PROGRAMMABLE OUTPUT RECEPTACLES (5-15R)

NOTES

1. UNIT DIMENSIONS (WxDxH) 430mm x 476mm x 85mm (2U)  
(16.9") x (18.7") x (3.3")
2. UNIT WEIGHT 18.5kg (40.8lbs)
3. SHIPPING DIMENSIONS (WxDxH) 542mm x 583mm x 228mm  
(21.3") x (23.0") x (9.0")
4. SHIPPING WEIGHT 24kg (52.9lbs)
5. MINIMUM AIRFLOW CLEARANCE IS 100mm (4.0")  
FRONT AND REAR.

SHEET NO. 1 OF 1	DRAWN BY: P BENNER	TITLE <b>OUTLINE DRAWING LIEBERT GXT5 LITHIUM-ION 1500VA 100-120VAC RACK/TOWER UPS</b>
CO. NO. -	DESIGNED BY: P BENNER	
REF DWG. -	APPROVED BY: N SECORD	

DWG. NO. GXT5_LI_1500_120	1050 DEARBORN DR P.O. BOX 29186 COLUMBUS, OH 43229
DATE (LATEST REV.) 2/14/2022	
REVISION 0	

