

# CYBEX™ SC900XD SECURE DESKTOP KVM SWITCHES



Superior security and control at the desktop  
NIAPP PP 3.0 Compliant, Common Criteria Tested and Certified

## OVERVIEW

### KEY FEATURES

- Advanced isolation between computers and shared peripherals
- Support for both DVI-I and DisplayPort 1.2 for direct connection to thin clients and PCs
- Use for two monitors, or pair with Vertiv extension technology to send to a central display

### BENEFITS

- Compliant to NIAP Protection Profile for Peripheral Sharing Switches, version 3.0
- Unidirectional Optical Data Diodes assure USB peripheral isolation enabling data flow from devices to host only
- Always-on active anti-tampering system
- Dedicated Peripheral Port (DPP) for connecting authentication devices such as biometric readers and smart card readers
- Hardware-based peripheral isolation loads all firmware on ROM with no keyboard buffering or memory
- Full USB device filtering to assure support for keyboard and mouse only
- Mouse and keyboard switching via emulation assures zero delay in switching time between connected sources



SPECIFICATIONS		
MODEL NUMBER	SC920XD	SC945XD
System Connections	2	4
System Support	HDMI 1.4	
Display Connections	2	2
Display Support	DVI-I single-link/dual-link and DisplayPort 1.2	
Max Resolution	DVI dual-link 2560x1600 to UHD 4K @ 60 Hz	
CONNECTIONS		
Console Peripherals	USB Type - A	
Computer Peripherals	USB Type - B	
Dedicated Peripheral Port	0	1
Audio Input/Output	1 x 3.5 mm stereo female	
MECHANICAL		
Enclosure	Steel with plastic front panel	
Dimensions W x D x H in / (mm)	7 x 2.4 x 1.7 in 177 x 61 x 42 mm	13.7 x 5 x 1.7 in 342 x 125 x 42 mm
Weight lbs / (kg)	1.0 lbs (0.5 kg)	3.0 lbs (1.5 kg)
POWER		
Power Requirements	12V DC 1.5A Power Adapter	35W Max Internal
AC Input Voltage	100 to 240V AC	
ENVIROMENTAL		
Operating Temperature	32° to 104°F; 0° to 40°C	
Storage Temperature	-4° to 140°F; -20° to 60°C	
Humidity	0-80% RH, non-condensing	
Certifications	CE, RCM, FCC class B, VCCI, TUV US, TUV Canada	
Warranty	3 years	



SC920XD Rear Panel



SC945XD Rear Panel

### Ordering Details

MODEL NUMBER	CABLE OPTIONS-LENGTH	CABLE DESCRIPTION
SC920XD	CBL0178 - 6 ft.	1 DVI-D/1 DISPLAYPORT/1 USB/1 AUDIO
SC945XD	CBL0179 - 6 ft.	1 DVI-D/1 DISPLAYPORT/2 USB/1 AUDIO



VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.