


Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



NEMA L21-20P  
 (20 A, 3/N/PE, 100-120/173-208 V)

NEMA L21-20P

AGENCY COMPLIANCE:  
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07  
 - FCC certification  
 - CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:  
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:  
 1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W  
 2. UNIT WEIGHT: 4 kg / 8.8 lbs  
 3. SHIPPING DIMENSIONS: 2017.0 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W  
 4. SHIPPING WEIGHT: 6.8 kg / 15 lbs  
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

BANK	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BANK
A	L1	12xNEMA 5-20	100-120	16	16
B	L2-L3	10xC13, 2xC19	173-208	12/16	16
C	L2-L3	10xC13, 2xC19	173-208	12/16	16

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	NEMA L21 - 20P	3/N/PE	50/60	100-120/173-208	20	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
Date		Name		Bezeichnung / Description	
07/01/16		Blass		MPH2-NBV_L21-20P_20N-40-12A	
07/01/16		Votýpka		Input and Branch Metered	
-		-		Zeichnungs-Nr. / Drawing no.	
-		-		MPHB1421	
-		-		Maßstab Scale	
-		-		1:5	
-		-		Verwendet in / Used in	
-		-		Blatt/Sheet	
-		-		1/1	
Rev.	Change	Date	Name		
C	18131	05.06.2017	Petrů		