



BACnet Protocol Implementation Conformance Statement

Reference Guide
iCOM - High Definition

The information contained in this document is subject to change without notice and may not be suitable for all applications. While every precaution has been taken to ensure the accuracy and completeness of this document, Vertiv assumes no responsibility and disclaims all liability for damages resulting from use of this information or for any errors or omissions. Refer to other local practices or building codes as applicable for the correct methods, tools, and materials to be used in performing procedures not specifically described in this document.

The products covered by this instruction manual are manufactured and/or sold by Vertiv. This document is the property of Vertiv and contains confidential and proprietary information owned by Vertiv. Any copying, use or disclosure of it without the written permission of Vertiv is strictly prohibited.

Names of companies and products are trademarks or registered trademarks of the respective companies. Any questions regarding usage of trademark names should be directed to the original manufacturer.

Technical Support Site

If you encounter any installation or operational issues with your product, check the pertinent section of this manual to see if the issue can be resolved by following outlined procedures. Visit <https://www.VertivCo.com/en-us/support/> for additional assistance.

TABLE OF CONTENTS

1 BACnet Protocol Implementation Conformance Statement	1
1.1 BIBBs Support	1
1.2 Segmentation Capability	1
1.3 Supported Services	2
1.4 Standard Object Types Supported	2
1.5 Object Properties	3
1.5.1 Device Object	3
1.5.2 Analog Object	4
1.5.3 Binary Object Properties	6
1.5.4 Multi-state Object Properties	7

1 BACNET PROTOCOL IMPLEMENTATION CONFORMANCE STATEMENT

Vendor Name: Vertiv™

Product Name: iCOM - High Definition

Product Model Number: iCOM - High Definition

BACnet Protocol Version.Revision: 1.12

The Liebert iCOM - High Definition card provides access to Vertiv™ devices via the BACnet protocol. The BACnet protocol support in the IntelliSlot platform has been tested by the BACnet Testing Laboratories (BTL) and certified to be compliant with the BACnet protocol standards. The BTL listing for iCOM - High Definition on the BACnet International website can be found [here](#).

This document describes the Services and Objects supported in the Unity BACnet protocol implementation. Data points of the managed device are mapped to BACnet objects that are automatically created in the card when the device is discovered. The connection is a 10/100BaseT Ethernet port that supports device-data access using BACnet/IP, or an RS-485 port that supports device-data access using BACnet MSTP. A web interface provides access to device information as well as card configuration and administration.

1.1 BIBBs Support

NAME	DESCRIPTION
DS-RP-B	Data Sharing - ReadProperty-B
DS-RPM-B	Data Sharing - ReadPropertyMultiple-B
DS-WP-B	Data Sharing - WriteProperty-B
DS-WPM-B	Data Sharing - WritePropertyMultiple-B
DS-COV-B	Data Sharing - COV-B
DM-DDB-B	Device Management - Dynamic Device Binding-B
DM-DOB-B	Device Management - Dynamic Object Binding-B
DM-TS-B	Device Management - TimeSynchronization-B
DM-UTC-B	Device Management - UTCTimeSynchronization-B

1.2 Segmentation Capability

Not supported.

1.3 Supported Services

SERVICE	INITIATE	EXECUTE
ConfirmedCOVNotification	x	
UnconfirmedCOVNotification	x	
SubscribeCOV		x
SubscribeCOVProperty		
Object Access Services		
ReadProperty		x
ReadPropertyMultiple		x
WriteProperty		x
WritePropertyMultiple		x
Remote Device Management Services		
TimeSynchronization		x
UTCTimeSynchronization		x
Who-Has		x
I-Have	x	
Who-Is		x
I-Am	x	

1.4 Standard Object Types Supported

OBJECT TYPE	X = SUPPORTED
Analog Input	x
Analog Output	x
Analog Value	x
Binary Input	x
Binary Output	x
Binary Value	x
Device	x
Multi-state Input	x
Multi-state Output	x
Multi-state Value	x

1.5 Object Properties

The following object properties are supported. All properties are read-only unless otherwise noted.

1.5.1 Device Object

The Device object represents the agent (the card) rather than the managed device.

PROPERTY	COMMENTS
Object_Identifier	The card must be configured with a unique Device Instance Number to avoid interference with other cards on the same BACnet network.
Object_Name	Writable. If the Device Object Name is changed from the default, the configured name must be unique to avoid interference with other cards on the same BACnet network.
Object_Type	
System_Status	
Vendor_Name	
Vendor_Identifier	
Model_Name	
Firmware_Revision	
Application_Software_Version	
Location	
Description	
Protocol_Version	
Protocol_Revision	
Protocol_Services_Supported	
Protocol_Object_Types_Supported	
Object_List	
Max_APDU_Length_Accepted	
Segmentation_Supported	
Local_Time	
Local_Date	
UTC_Offset	
Daylight_Savings_Status	
APDU_Timeout	Writable. Range: 1-65,535 ms. Default 3000 ms.
Number_Of_APDU_Retries	Writable. Range: 0-8. Default 3.
Device_Address_Binding	
Database_Revision	
Active_COV_Subscriptions	

1.5.2 Analog Object

PROPERTY	ANALOG INPUT	ANALOG OUTPUT	ANALOG VALUE	COMMENTS
Object_Identifier	x	x	x	
Object_Name	x	x	x	
Object_Type	x	x	x	
Present_Value	x	x	x	Writable if 1) object is Analog Output, or 2) object is Analog Value and the associated device data point is writable, or 3) Out_Of_Service is True
Description	x	x	x	
Status_Flags	x	x	x	
Event_State	x	x	x	
Reliability	x	x	x	
Out_Of_Service	x	x	x	Writable. Values: True/False. Default: False.
Units	x	x	x	See below.
Priority_Array		x	(x)	Supported in analog objects that map to writable data points.
Relinquish_Default		x	(x)	Supported in analog objects that map to writable data points. The value is equal to the Present_Value so that if all entries in the Priority_Array are relinquished, the Present_Value does not change.
COV_Increment	x	x	x	Writable. Default: 0.5.

Units

Possible values of the Units property includes the BACnet Engineering Units defined in the BACnet standard, plus these additional proprietary units values:

VALUE	UNITS
256	Ampere-Hours
257	MiliHertz (.001Hertz)
258	GigaHertz (1,000,000,000 Hertz)
259	PSI - Absolute
260	Total Harmonic Distortion (%)
261	Microhms (.000001 Ohms)
262	Bytes
263	Kilobytes
264	Megabytes
265	Gigabytes
266	Terabytes
267	Volt-Ampere-Hours
268	KiloVolt-Ampere-Hours
269	Volt-Ampere-Reactive-Hours
270	KiloVolt-Ampere-Reactive-Hours
271	Grams of Water per Cubic Meter of Air
272	Torrs
273	MilliTorr

1.5.3 Binary Object Properties

PROPERTY	BINARY INPUT	BINARY OUTPUT	BINARY VALUE	COMMENTS
Object_Identifier	x	x	x	
Object_Name	x	x	x	
Object_Type	x	x	x	
Present_Value	x	x	x	Writable if 1) object is Binary Output, or 2) object is Binary Value and the associated device data point is writable, or 3) Out_Of_Service is True
Description	x	x	x	
Status_Flags	x	x	x	
Event_State	x	x	x	
Reliability	x	x	x	
Out_Of_Service	x	x	x	Writable. Values: True/False. Default: False.
Polarity	x	x		
Inactive_Text	x	x	x	
Active_text	x	x	x	
Priority_Array		x	(x)	Supported in binary objects that map to writable data points.
Relinquish_Default		x	(x)	Supported in binary objects that map to writable data points. The value is equal to the Present_Value so that if all entries in the Priority_Array are relinquished, the Present_Value does not change.

1.5.4 Multi-state Object Properties

PROPERTY	MULTI-STATE INPUT	MULTI-STATE OUTPUT	MULTI-STATE VALUE	COMMENTS
Object_Identifier	x	x	x	
Object_Name	x	x	x	
Object_Type	x	x	x	
Present_Value	x	x	x	Writable if 1) object is Multi-state Output, or 2) object is Multi-state Value and the associated device data point is writable, or 3) Out_Of_Service is True
Description	x	x	x	
Status_Flags	x	x	x	
Event_State	x	x	x	
Reliability	x	x	x	
Out_Of_Service	x	x	x	Writable. Values: True/False. Default: False.
Number_Of_States	x	x	x	
State_Text	x	x	x	
Priority_Array		x	(x)	Supported in multi-state objects that map to writable data points.
Relinquish_Default		x	(x)	Supported in multi-state objects that map to writable data points. The value is equal to the Present_Value so that if all entries in the Priority_Array are relinquished, the Present_Value does not change.

This page intentionally left blank





VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

SL-70399_REVO/590-2224-501A