



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugelassen. Alle Rechte vorbehalten.



**OUTPUT POWER**

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	3x C13, 1x C19	200-240	12/16	16
B	L2-L3	3x C13, 1x C19	200-240	12/16	16
C	L3-L1	3x C13, 1x C19	200-240	12/16	16
D	L1-L2	3x C13, 1x C19	200-240	12/16	16
E	L2-L3	3x C13, 1x C19	200-240	12/16	16
F	L3-L1	3x C13, 1x C19	200-240	12/16	16

**INPUT POWER**

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
-	-	3/PE	50/60	200-240	60	48

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

**AGENCY COMPLIANCE:**  
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07  
 - FCC certification  
 - CB certification: IEC 60950-1 (2nd)  
 - "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H22)

**ENVIRONMENTAL RATING:**  
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:**  
 1. UNIT DIMENSIONS: 1826.5 mm (71.9") H x 50 mm (2.0") D x 56 mm (2.2") W  
 2. UNIT WEIGHT: 4 kg / 8.8 lbs  
 3. SHIPPING DIMENSIONS: 2017 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W  
 4. SHIPPING WEIGHT: 6.8 kg / 15 lbs  
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
Dimensions in mm	Drawn	05/02/16	Name	Bezeichnung / Description	
	Checked	05/02/16	Blass	MPH2-NCV_3P4W-60A_18N-60_HW	
	Approved	-	Votýpka	Input and Branch Metered + Outlet Switched	
				Zeichnungs-Nr. / Drawing no.	Maßstab Scale
				MPHC1156	
Rev.	Change	Date	Name	Verwendet in / Used in	Blatt/Sheet
B	18131	02.06.2017	Petrů	-	1/1