



Vertiv™ Lithium-Ion UPS Catalog

Vertiv™ Lithium-ion UPS
1,000 – 10,000VA
Rackmount and Tower




Table of Contents

Portfolio	3
Vertiv™ Liebert® PSI5 Lithium-Ion UPS	4
1.1 Models	4
1.2 Specifications	5
Vertiv™ Liebert® GXT5 Lithium-Ion UPS 1-3kVA 120VAC	6
1.1 Models	6
1.2 Specifications	7
Vertiv™ Liebert® GXT5 Lithium-Ion UPS 5-10kVA 120/208VAC	8
1.1 Models	8
1.2 Specifications	9
Power Assurance Services	10

Why should you choose Lithium-Ion Technology?


Longer Life



Lowest TCO



Smaller and Lighter



Longer Runtime



Resilient to Heat



Fast Battery Recharge



Environmentally Friendly

- Lithium-ion batteries require less onsite maintenance, reducing truck rolls and avoiding associated carbon emissions
- Lithium-ion batteries have a longer life, reducing waste and material consumption
- Lithium-ion batteries use less material for equal output and up to 99% of the battery elements are recyclable

Upgrading to a Vertiv™ Lithium-ion UPS is a win for your business and the environment.

Industry Leading Portfolio of Lithium-ion UPS

Vertiv™ Liebert® PSI5 Lithium-ion UPS



- Line-Interactive UPS with AVR
- 1,500 – 3,000VA
- Rack/Tower Convertible
 - Tower & Short Depth Options
- 4-6ms Transfer Time to Battery

Great For:

- Network Closets
- Server Rooms
- Wall-mount & 2 Post racks
- Retail Kiosks
- E-Rate eligible

Vertiv™ Liebert® GXT5 Lithium-ion UPS



- Online Double-Conversion
- 1,000 – 10,000VA
- Rack/Tower Convertible
 - Scalable Runtime Options
- Zero Transfer Time to Battery

Great For:

- Network Closets
- Server Rooms
- Edge Data Centers, IDF/MDF
- Mission critical equipment
- E-Rate eligible

Lithium-Ion Outperforms VRLA when compared...


Battery Feature	VRLA Battery	Lithium-Ion Battery	Lithium-Ion Benefit
Standard battery life	3-5 years	8-10 years	Up to 3 times longer life
Typical cycle life	200-260	2000	Up to 10x more discharge/recharge cycles
Battery recharge time (@ 90%)	3-6 hours	<2 hours	Fast recovery time safeguards your critical IT equipment in the event of multiple outages
Battery weight	35 kg	22 kg	45% lighter making it ideal for small spaces and wall-mount racks
Warranty	2 or 3 years	5 years	Worry free operation so you can set-it and forget-it

Vertiv™ Liebert® PSI5 Lithium-Ion UPS Models


1,500-3,000VA 120VAC

The Liebert® PSI5 Lithium-Ion also includes automatic voltage regulation (AVR) technology, which protects against utility voltage fluctuation, extends battery life by maximizing time on utility power, and provides premium protection from power disturbances. In battery mode, the Liebert PSI5 delivers pure sine wave output to protect sensitive servers and networking equipment. With up to 9 minutes of runtime at full load and 20 minutes at half load – more than comparable competing models – the Liebert PSI5 Lithium-Ion provides plenty of runtime during an outage for an orderly shutdown. It comes with a rotating LCD display to allow both rack and tower configurations, provides real time information regarding UPS status and operating conditions, and supports remote monitoring. It's also highly energy efficient, delivering up to 98% efficiency at full load in normal operating mode. You can rest assured your business is protected with this Vertiv™ solution, which includes a 5-year full standard warranty.


Liebert® PSI5-1500RT120LI




Liebert® PSI5-2200RT120LI



Liebert® PSI5-3000RT120LI




Liebert® PSI5-3000SRT120LI



- A** RJ-45 Data Line Surge Connectors
- B** USB Port
- C** Output Receptacles
- D** Input Power Cord
- E** Input Circuit Breaker
- F** Emergency Power Off (EPO) Connector
- G** Liebert® IntelliSlot™ (Optional Communications Card)
- H** Programmable Outlet Group
- I** NEMA L5-30R Output Receptacle
- J** NEMA L5-20R Output Receptacle

Liebert® PSI5-1500MT120LI



Vertiv™ Liebert® PSI5 Lithium-Ion UPS Specifications

1,500-3,000VA 120VAC

Standard Models*	PSI5-1500MT120LI	PSI5-1500RT120LI	PSI5-2200RT120LI	PSI5-3000RT120LI	PSI5-3000SRT120LI
Form Factor	Mini Tower	2U Rack/Tower	2U Rack/Tower	2U Rack/Tower	3U Rack/Tower
Power Rating	1500VA / 1350W	1500VA / 1350W	1920VA / 1920W	3000VA / 2700W	3000VA / 2700W
Dimensions, W X D X H, IN (MM)					
Unit	6.3 x 15.6 x 8.7 (158 x 397 x 220)	17.2 x 16.2 x 3.4 (438 x 411 x 86)	17.2 x 20.1 x 3.4 (438 x 510 x 86)	17.2 x 24.8 x 3.4 (438 x 630 x 86)	17.3 x 16.9 x 5.14 (438 x 430 x 130.6)
Rackmount depth	-	15 (380)	18.9 (480)	23.62 (600)	15.7 (400)
Shipping	9.1 x 19.5 x 12.8 (230 x 495 x 325)	10.2 x 22.9 x 22.4 (258 x 582 x 570)	10.2 x 26.5 x 22.4 (258 x 672 x 570)	10.2 x 30.8 x 21.7 (258 x 782 x 550)	26.4 x 22.4 x 11.1 (670 x 570 x 282)
Weight, LB (KG)					
Unit	27.9 (12.7)	28.3 (12.9)	39.5 (18.0)	53.5 (24.3)	56 (25.4)
Shipping	31.2 (14.2)	42.1 (19.1)	53.8 (24.4)	67.9 (30.8)	67.9 (30.8)
Input/Output AC Parameters					
Input Plug	NEMA 5-15P (90deg type)	NEMA 5-15P	NEMA L5-20P (5-20 Adapter included)	NEMA L5-30P	NEMA L5-30P
Input Cord	6ft (1.8m) Attached	10ft (3m) Attached	10ft (3m) Attached	10ft (3m) Attached	10ft (3m) Attached
Non-Programmable Receptacles	(3) NEMA 5-15R	(3) NEMA 5-15R	(1) NEMA L5-20R, (3) NEMA 5-20R	(1) NEMA L5-30R, (3) NEMA 5-20R	(1) NEMA L5-30R, (6) NEMA 5-15/20R
Programmable Receptacles	(3) NEMA 5-15R	(3) NEMA 5-15R	(3) NEMA 5-20R	(3) NEMA 5-20R	(3) NEMA 5-15/20R
Nominal Voltage Setting	120VAC Default; 100/110/115/125VAC User Selectable				
Voltage Range Without Battery Operation	75 - 146VAC				
Frequency Range	55-65Hz (57-63Hz Battery to Normal Comeback)				
Surge Protection	ANSI C62.41, Category A, Level 3				ANSI C62.41, Category B
Transfer Time	4 - 6ms Typical				
Battery Waveform	Pure Sine Wave				
Efficiency					
Normal (Line) Mode	97.1%	97.1%	97.1%	97.3%	97.3%
Battery Parameters					
Type	Lithium-Ion (LiFePO4)				
Recharge Time (from full discharge)	2hrs to 90%	2hrs to 90%	2hrs to 90%	2hrs to 90%	2hrs to 90%
Full-Load Runtime	7.5 min	7.5 min	8.6 min	8.9 min	7.7 min
Half-Load Runtime	17.7 min	17.7 min	19.0 min	20.0 min	18.3 min
Environmental					
Operating Temperature,*F (°C)	32° to 104° (0° to 40°)				
Storage Temperature *F (°C)	5° to 120° (-15° to 50°)				
Relative Humidity	20% - 90%, non-condensing				
Operating Altitude, ft (m)	0 to 9,942 (0 to 3,000) without derating. Operating temperature reduced 9°F (5 °C) for each additional 1,640ft (500m) of altitude				
Audible Noise	< 45 dB @ line mode, < 55 dB @ battery mode				
Certifications					
Safety	UL 1642 (LiFe cells), UL 1973 (LiFe pack), UL 1778, CSA 22.2 no. 107.3				
Agency	UL 1778, c-UL, NOM, FCC Part 15, Class B				
Environmental	RoHS2 / REACH / WEEE				
Network Surge	ANSI C62.41, Category A, Level 3				
Transportation	ISTA Procedure 2A UN 38.3 (Lithium-ion)				
Warranty	5 years on UPS and Battery				
Protection Plan					
Equipment Protection Plan	\$400,000				

*Liebert PSI5 2U Rack/Tower UPS + RDU120 card bundles available - Add an "N" to the end of the model number. Available through select distributors."

Vertiv™ Liebert® GXT5 Lithium-Ion UPS Models

1-3kVA 120VAC


1000-1500VA – 120V Rack/Tower

External Battery Connector

Scalable runtime solution supported for extended outage protection (up to 8 External Battery Cabinets)

4 x Individually Controllable Receptacle

Manage load on battery and control unauthorized access to UPS receptacle



Communications

IntelliSlot™ (Web/SNMP Card), Serial Port, Dry Contacts, USB Port for Local and Remote Configuration and UPS Management

NEMA 5/15P input with over current protection

Simple installation and power on with connected input cord

2000VA – 120V Rack/Tower

External Battery Connector

Scalable runtime solution supported for extended outage protection (up to 8 External Battery Cabinets)

NEMA L5-20R

Support larger devices or rack PDU

4x Individually Controllable Receptacle, 2x Always on Receptacles

Manage load on battery and control unauthorized access to UPS receptacle



Communications

IntelliSlot™ (Web/SNMP Card), Serial Port, Dry Contacts, USB Port for Local and Remote Configuration and UPS Management

NEMA L5-20P input with over current protection

Includes NEMA 5-20 Adapter for non-locking receptacles

3000VA – 120V Rack/Tower

External Battery Connector

Scalable runtime solution supported for extended outage protection (up to 8 External Battery Cabinets)

NEMA L5-30R

Support larger devices or rack PDU

4x Individually Controllable Receptacle, 2x Always on Receptacles

Manage load on battery and control unauthorized access to UPS receptacle



Communications

IntelliSlot™ (Web/SNMP Card), Serial Port, Dry Contacts, USB Port for Local and Remote Configuration and UPS Management

NEMA L5-30P input with over current protection

Simple installation and power on with connected input cord

Vertiv™ Liebert® GXT5 Lithium-Ion UPS Specifications

1-3kVA 120VAC

Standard Models Models with RDU101 Network Card*	GXT5LI-1000LVRT2UXL GXT5LI-1000LVRT2UXLN	GXT5LI-1500LVRT2UXL GXT5LI-1500LVRT2UXLN	GXT5LI-2000LVRT2UXL GXT5LI-2000LVRT2UXLN	GXT5LI-3000LVRT2UXL GXT5LI-3000LVRT2UXLN
Form Factor	2U Rack/Tower	2U Rack/Tower	2U Rack/Tower	2U Rack/Tower
Power Rating	1000VA / 1000W	1500VA / 1350W	2000VA / 1800W	3000VA / 2700W
Dimensions, W X D X H, IN (MM)				
Unit	16.9 x 17.3 x 3.4 (430 x 446 x 85)	16.9 x 18.7 x 3.4 (430 x 476 x 85)	16.9 x 18.7 x 3.4 (430 x 476 x 85)	16.9 x 21.5 x 3.4 (430 x 546 x 85)
Shipping	22.4 x 23.5 x 9.5 (570 x 597 x 242)	22.4 x 23.5 x 9.5 (570 x 597 x 242)	22.4 x 23.5 x 9.5 (570 x 597 x 242)	22.4 x 28.2 x 9.5 (717 x 242)
Weight, LB (KG)				
Unit	37.5lbs (17kg)	39.7lbs (18kg)	39.7lbs (18kg)	48.5lbs (22kg)
Shipping	47.6lbs (21.6kg)	52.9lbs (24kg)	52.9lbs (24kg)	59.7lbs (27.1kg)
Input/Output AC Parameters				
Input Plug	NEMA 5-15P	NEMA 5-15P	NEMA L5-20P	NEMA L5-30P
Input Cord	10ft (3m) Attached	10ft (3m) Attached	10ft (3m) Attached L5-20 To 5-20P Adapter	10ft (3m) Attached
Total Receptacles	(6) NEMA 5-15R	(6) NEMA 5-15R	(1) NEMA L5-20R, (6) NEMA 5-15/20R	(1) NEMA L5-30R, (6) NEMA 5-15/20R
Programmable Receptacles	(4) NEMA 5-15R	(4) NEMA 5-15R	(4) NEMA 5-15/20R	(4) NEMA 5-15/20R
Nominal Voltage Setting	120VAC Default; 100/110/115/120V/125VAC (User-Configurable)	120VAC Default; 100/110/115/120V/125VAC (User-Configurable)	120VAC Default; 100/110/115/120V/125VAC (User-Configurable)	120VAC Default; 100/110/115/120V/125VAC (User-Configurable)
Voltage Range Without Battery Operation	Nominal (Full Load): 102 - 150 VAC; Maximum: 60 - 150 VAC	Nominal (Full Load): 102 - 150 VAC; Maximum: 60 - 150 VAC	Nominal (Full Load): 102 - 150 VAC; Maximum: 60 - 150 VAC	Nominal (Full Load): 102 - 150 VAC; Maximum: 60 - 150 VAC
Frequency Range	40-70Hz	40-70Hz	40-70Hz	40-70Hz
Surge Protection	ANSI C62.41, Category B	ANSI C62.41, Category B	ANSI C62.41, Category B	ANSI C62.41, Category B
Transfer Time	0 ms	0 ms	0 ms	0 ms
Battery Waveform	Pure Sine Wave	Pure Sine Wave	Pure Sine Wave	Pure Sine Wave
Battery Parameters				
Type	Lithium-Ion (LiFePO4)	Lithium-Ion (LiFePO4)	Lithium-Ion (LiFePO4)	Lithium-Ion (LiFePO4)
Recharge Time (from full discharge)	< 2 hrs to 90%	< 2 hrs to 90%	< 2 hrs to 90%	< 2 hrs to 90%
Full-Load Runtime	13 min	14 min	10.5 min	6.5 min
Half-Load Runtime	28 min	28 min	22.5 min	15 min
External Battery Cabinet	VEBCLI-48VRT1U	VEBCLI-48VRT1U	VEBCLI-48VRT1U	VEBCLI-48VRT1U
Environmental				
Operating Temperature, °F (°C)	32°F to 104°F (0°C to 40°C) (10% Derating at 50°C)	32°F to 104°F (0°C to 40°C) (10% Derating at 50°C)	32°F to 104°F (0°C to 40°C) (10% Derating at 50°C)	32°F to 104°F (0°C to 40°C) (10% Derating at 50°C)
Storage Temperature °F (°C)	-4° to 140° (-20° to 60°)	-4° to 140° (-20° to 60°)	-4° to 140° (-20° to 60°)	-4° to 140° (-20° to 60°)
Relative Humidity	0% - 95%, non-condensing	0% - 95%, non-condensing	0% - 95%, non-condensing	0% - 95%, non-condensing
Operating Altitude, ft (m)	0 to 10,000 (0 to 3,000) w/o Derating (15% Derating at 4000m)	0 to 10,000 (0 to 3,000) w/o Derating (15% Derating at 4000m)	0 to 10,000 (0 to 3,000) w/o Derating (15% Derating at 4000m)	0 to 10,000 (0 to 3,000) w/o Derating (15% Derating at 4000m)
Audible Noise	< 48 dB	< 48 dB	< 48 dB	< 48 dB
Certifications				
Safety	UL 1642 (Li-Ion Battery Cells), UL 1973 (Li-Ion Battery Pack w/UPS), UL 1778, CSA 22.2 No. 107.3	UL 1642 (Li-Ion Battery Cells), UL 1973 (Li-Ion Battery Pack w/UPS), UL 1778, CSA 22.2 No. 107.3	UL 1642 (Li-Ion Battery Cells), UL 1973 (Li-Ion Battery Pack w/UPS), UL 1778, CSA 22.2 No. 107.3	UL 1642 (Li-Ion Battery Cells), UL 1973 (Li-Ion Battery Pack w/UPS), UL 1778, CSA 22.2 No. 107.3
Agency	UL 1778, c-UL, NOM, FCC Part 15, Class A	UL 1778, c-UL, NOM, FCC Part 15, Class A	UL 1778, c-UL, NOM, FCC Part 15, Class A	UL 1778, c-UL, NOM, FCC Part 15, Class A
Environmental	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE
Network Surge	IEC 61000-4-5, ANSI C62.41, Category B	IEC 61000-4-5, ANSI C62.41, Category B	IEC 61000-4-5, ANSI C62.41, Category B	IEC 61000-4-5, ANSI C62.41, Category B
Transportation	ISTA Procedure 2A	ISTA Procedure 2A	ISTA Procedure 2A	ISTA Procedure 2A
Warranty	5 years on UPS and Battery	5 years on UPS and Battery	5 years on UPS and Battery	5 years on UPS and Battery
Equipment Protection Plan	Up To \$500,000 (For Covered Equipment)	Up To \$500,000 (For Covered Equipment)	Up To \$500,000 (For Covered Equipment)	Up To \$500,000 (For Covered Equipment)

*Liebert® GXT5 Lithium-Ion Rack/Tower UPS + RDU101 card bundles available through select distributors in North America (by adding an "N" at the end of the standard model number)

Vertiv™ Liebert® GXT5 Lithium-Ion UPS Models

5-10kVA 120/208VAC

5000VA – 120V/208V MV Rack/Tower

Communications

IntelliSlot™ (Web/SNMP Card),
Serial Port, Dry Contacts, USB Port
for Local and Remote Configuration
and UPS Management

External Battery Connector

Scalable runtime solution supported for extended
outage protection (up to 8 External Battery Cabinets)




6000VA – 120V/208V MV Rack/Tower

Communications

IntelliSlot™ (Web/SNMP Card),
Serial Port, Dry Contacts, USB Port
for Local and Remote Configuration
and UPS Management

External Battery Connector

Scalable runtime solution supported
for extended outage protection
(up to 8 External Battery Cabinets)




8000VA - 10,000 VA – 120V/208V MV Rack/Tower

Communications

IntelliSlot™ (Web/SNMP Card),
Serial Port, Dry Contacts, USB Port
for Local and Remote Configuration
and UPS Management

External Battery Connector

Scalable runtime solution supported
for extended outage protection
(up to 8 External Battery Cabinets)



Vertiv™ Liebert® GXT5 Lithium-Ion UPS Specifications


5-10kVA 120/208VAC

Standard Models	GXT5LI-5000MVRT3UXLN	GXT5LI-6000MVRT3UXLN	GXT5LI-8000MVRT4UXLN	GXT5LI-10KMVRT4UXLN
Form Factor	3U Rack/Tower		4U Rack/Tower	
Power Rating	5000 VA / 5000 W	6000 VA / 6000 W	8000 VA / 8000 W	10,000 VA / 10,000 W
Dimensions, W x D x H, in (mm)				
Unit	16.9 x 30 x 3.3 (2U) (430 x 865 x 85)	16.9 x 35.4 x 3.3 (2U) (430 x 900 x 85)	16.9 x 36.6 x 3.3 (2U) (430 x 930 x 85)	
Shipping	31.4 x 39.3 x 20.9 (798 x 900 x 532)		31.4 x 39.3 x 29.1 (798 x 900 x 739)	
Weight, Lb (Kg)				
Unit with EBCs*	104.9 (47.6)	100 (45.4)	156.3 (70.9)	
Unit without EBCs	56.4 (25.6)	51.5 (23.4)	59.3 (26.9)	
Shipping	176.3 (80)	158.7 (72)	247.7 (112.4)	
Input/Output AC Parameters				
Input Plug	NEMA L14-30P 3m (10ft) Attached	Hardwired (L1-L2-N-G)	Hardwired (L1-L2-N-G)	Hardwired (L1-L2-N-G)
Output	(2) NEMA L14-30R	Hardwired (L1-L2-N-G)	Hardwired (L1-L2-N-G)	Hardwired (L1-L2-N-G)
Nominal Voltage Setting	208VAC / 120VAC (Default); 240VAC / 120VAC (User-Configurable); ±1%			
Voltage Range Without Battery Operation	Nominal (Full Load); 90V - 150V AC (L-N); Maximum: 60 - 150VAC (L-N)			
Frequency Range	40-70Hz			
Surge Protection	ANSI C62.41, Category B			
Transfer Time	0 ms			
Battery Waveform	Pure Sine Wave			
Battery Parameters				
Type	Lithium-Ion (LiFePO4)			
Recharge Time (from full discharge)	< 2hrs to 90%	< 2hrs to 90%	< 2hrs to 90%	< 2hrs to 90%
Full-Load Runtime	12 min	10 min	13 min	10 min
Half-Load Runtime	25 min	21 min	27 min	21 min
Replacement Battery	N/A, external battery only	N/A, external battery only	N/A, external battery only	N/A, external battery only
External Battery Cabinet (quantity)	VEBCLI-192VRT1U (1)	VEBCLI-192VRT1U (1)	VEBCLI-192VRT1U (2)	VEBCLI-192VRT1U (2)
Environmental Requirements				
Operating Temperature, °F (°C)	32°F to 104°F (0°C to 40°C) (10% Derating at 50°C)			
Storage Temperature °F (°C)	-4° to 140° (-20° to 60°)			
Relative Humidity	0% - 95%, non-condensing			
Operating Altitude, ft (m)	0 to 10,000 (0 to 3,000) w/o Derating. (15% Derating at 4000m)			
Audible Noise	< 58 dB			
Certifications				
Safety	UL 1642 (Li-Ion Battery Cells), UL 1973 (Li-Ion Battery Pack w/UPS), UL 1778, CSA 22.2 No. 107.3			
Agency	UL 1778, c-UL, NOM, FCC Part 15, Class A			
Environmental	RoHS2 / REACH / WEEE			
Network Surge	IEC 61000-4-5, ANSI C62.41, Category B			
Transportation	ISTA Procedure 2A			
Warranty	5 years on UPS and Battery			
Protection Plan				
Equipment Protection Plan	Up To \$500,000 (For Covered Equipment)			

*Liebert GXT5 Lithium-Ion 5kVA and 6kVA units come equipped with (1) EBC. GXT5 Lithium-Ion 8kVA and 10kVA units come equipped with (2) EBCs,

Power Assurance Services

Power Assurance Package - Summary



- Includes all "Power Start-up Services" and "Power Emergency Services" support

Power Startup Services - Summary

- Installation includes mounting and start-up of new UPS (excludes hard-wired applications)
- Services performed by Vertiv factory trained technician
- Services performed 7 X 24, excluding national holidays within the 48 contiguous states and Hawaii
- Removal and disposal of existing UPS or equipment, if selected

Power Emergency Services - Summary

- On Site Service Support
- Full-service five (5) year contract term commencing upon the start-up date
- 100% parts coverage, including internal batteries, POD and web card
- 100% labor and travel coverage 7 days/week, 24 hours/day
- 24-Hour Customer Resolution Center via 1-800-LIEBERT
- Access to Customer Services Network portal

Vertiv™ LIFE™ Services includes above plus:

- Continuous Monitoring, Expert Analysis, and Proactive Response

Note: LIFE™ Services requires a Network Card.

Please refer to the appropriate Scope of Work for additional details.

Vertiv™ Liebert® PSI5 Lithium-Ion

Power Assurance Package				
Bundled Start-up Service AND 5-Year On-site Emergency Response	Standard	With LIFE™ Services	With Removal	With LIFE™ and Removal
Equipment Model / Type	Part Number	Part Number	Part Number	Part Number
Liebert PSI5 Lithium-Ion UP TO 3KVA	PAPPSI-1K3KLI	PAPPSI-1K3KLILF	PAPPSI-1K3KLIRMV	PAPPSI-1K3KLIRLF

Power Startup Services		
Startup Service Only	Standard	With Removal
Equipment Model / Type	Part Number	Part Number
Liebert PSI5 Lithium-Ion UP TO 3KVA	SUPSI-1k3k	SUPSI-1k3krmv

Power Emergency Services		
5-Year On-site Emergency Coverage - Only	Standard	With LIFE™ Services
Equipment Model / Type	Part Number	Part Number
Liebert PSI5 Lithium-Ion 1500VA	PEPPSI-1500LI5Y	PEPPSI-1500LILF
Liebert PSI5 Lithium-Ion 2200VA	PEPPSI-2200LI5Y	PEPPSI-2200LILF
Liebert PSI5 Lithium-Ion 3000VA	PEPPSI-3000LI5Y	PEPPSI-3000LILF

Vertiv™ Liebert® GXT5 Lithium-Ion, 1-3kVA

Power Assurance Package

Bundled Start-up Service AND 5-Year On-site Emergency Response	Standard	With LIFE™ Services	With Removal	With LIFE™ and Removal
Equipment Model / Type	Part Number	Part Number	Part Number	Part Number
Liebert GXT5 LI UP TO 3 KVA	PAPGXTLI-1K3K	PAPGXTLI-1K3KLF	PAPGXTLI-1K3KRMV	PAPGXTLI-1K3KRLF
External Battery Cabinets (48V)	PAPGXTLI-48VBATT	N/A	PAPGXTLI-48VBATTRMV	N/A

Power Startup Services

Startup Service Only	Standard	With Removal
Equipment Model / Type	Part Number	Part Number
Liebert GXT5 LI UP TO 3 KVA	SUGXT-1K3K	SUGXT-1K3KRMV
External Battery Cabinet (48V)	SUGXT-EXTBTBCTB	SUGXT-EXTBTBCTBRMV

Power Emergency Services

5-Year On-site Emergency Coverage - Only	Standard	With LIFE™ Services
Equipment Model / Type	Part Number	Part Number
Liebert GXT5 LI 1-3 KVA	PEPGXTLI-1K3K5YR	PEPGXTLI-1K3KLF
Lithium-Ion External Battery Cabinet 48V	PEPGXTLI-48VBAT5YR	N/A

Vertiv™ Liebert® GXT5 Lithium-Ion, 5-10kVA

Power Assurance Package

Bundled Start-up Service AND 5-Year On-site Emergency Response	Standard	With LIFE™ Services	With Removal	With LIFE™ and Removal
Equipment Model / Type	Part Number	Part Number	Part Number	Part Number
Liebert GXT5 LI 5KVA TO 6KVA	PAPGXTLI-5K6K	PAPGXTLI-5K6KLF	PAPGXTLI-5K6KRMV	PAPGXTLI-5K6KRLF
Liebert GXT5 LI 8KVA TO 10KVA	PAPGXTLI-8-10K	PAPGXTLI-8-10KLF	PAPGXTLI-8-10KRMV	PAPGXTLI-8-10KRLF
External Battery Cabinets (192V)	PAPGXTLI-192VBATT	N/A	PAPGXTLI-192VBATTRMV	N/A

Power Startup Services

Startup Service Only	Standard	With Removal
Equipment Model / Type	Part Number	Part Number
Liebert GXT5 LI 5KVA TO 6KVA	SUGXT-5-6U7	SUGXT-5-6U7RMV
Liebert GXT5 LI 8KVA TO 10KVA	SUGXT-8-10U7	SUGXT-8-10U7RMV
External Battery Cabinet (192V)	SUGXT-EXTBTBCTB	SUGXT-EXTBTBCTBRMV

Power Emergency Services

5-Year On-site Emergency Coverage - Only	Standard	With LIFE™ Services
Equipment Model / Type	Part Number	Part Number
Liebert GXT5 LI5-6KVA	PEPGXTLI-5K6K5YR	PEPGXTLI-5K6KLF
Liebert GXT5 LI8-10KVA	PEPGXTLI-8K10K5YR	PEPGXTLI-8K10KLF
Lithium-Ion External Battery Cabinet 192V	PEPGXTLI-192VBAT5YR	N/A



Vertiv.com | Vertiv Headquarters, 505 N Cleveland Ave, Westerville, OH 43082, USA

© 2025 Vertiv Group Corp. All rights reserved. Vertiv™ and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.