



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.



HARDWIRED TERMINAL DETAIL
(60 A, 3/PE, 200-240 V)

OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	4xC13, 1xC19	200-240	12/16	16
B	L2-L3	4xC13, 1xC19	200-240	12/16	16
C	L3-L1	4xC13, 1xC19	200-240	12/16	16
D	L1-L2	4xC13, 1xC19	200-240	12/16	16
E	L2-L3	4xC13, 1xC19	200-240	12/16	16
F	L3-L1	4xC13, 1xC19	200-240	12/16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
-	-	3/PE	50/60	200-240	60	48

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)
- "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H22)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

- UNIT DIMENSIONS: 1826.5 mm (71.9") H x 50 mm (2.0") D x 56 mm (2.2") W
- UNIT WEIGHT: 4 kg / 8.8 lbs
- SHIPPING DIMENSIONS: 2017 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
- SHIPPING WEIGHT: 6.8 kg / 15 lbs
- (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

	Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -
	-		-		-		-
Date		Name		Bezeichnung / Description			
07/01/16		Blass		MPH2-NBV_3P4W-60A_24N-60_HW			
Checked		Votýpka		Input and Branch Metered			
07/01/16		-		Zeichnungs-Nr. / Drawing no.			
Approved		-		MPHB1756			
-		-		Maßstab Scale			
-		-		1:5			
-		-		Verwendet in / Used in			
-		-		Blatt/Sheet			
-		-		1/1			
Rev.	Change	Date	Name				
C	18131	06.06.2017	Petrů				

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.