



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.


FRONT VIEW



REAR VIEW



UPPER VIEW



RoHS COMPLIANT

OUTPUT POWER


BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	1xC13, 2xC19	200-240	12/16	16
B	L2-L3	1xC13, 2xC19	200-240	12/16	16
C	L3-L1	2xC19	200-240	16	16
D	L1-L2	1xC13, 2xC19	200-240	12/16	16
E	L2-L3	1xC13, 2xC19	200-240	12/16	16
F	L3-L1	2xC19	200-240	16	16

METERING PARAMETER

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	IEC 60309	3/PE	50/60	200-240	60	48



AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

1. UNIT DIMENSIONS: 440 mm (17.3") W x 250 mm (9.8") D x 88 mm (3.5") H
2. UNIT WEIGHT: 8 kg / 17,6 lbs
3. SHIPPING DIMENSIONS: 543 mm (21.4") W x 485 mm (19.1") D x 240 mm (9.5") H
4. SHIPPING WEIGHT: 8,5 kg / 18,7 lbs
5. (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. BOTH SIDES CAN BE USED TO MOUNT THE PDU.

 Dimensions in mm		Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -													
		-		-		-		-													
<table border="1"> <tr> <td>Drawn</td> <td>27/05/16</td> <td colspan="2">Name</td> </tr> <tr> <td>Checked</td> <td>27/05/16</td> <td colspan="2">Racek</td> </tr> <tr> <td>Approved</td> <td>-</td> <td colspan="2">Votýpka</td> </tr> </table>		Drawn	27/05/16	Name		Checked	27/05/16	Racek		Approved	-	Votýpka		Date		Name		Bezeichnung / Description MPH2-NCC_3P4W-60A_4N-120 Input and Branch Metered + Outlet Switched			
		Drawn	27/05/16	Name																	
		Checked	27/05/16	Racek																	
Approved	-	Votýpka																			
-		-		Zeichnungs-Nr. / Drawing no. MPHC6325				Maßstab Scale 1:5													
Rev.		Change		Date		Name		Verwendet in / Used in -													
B		18154		13.06.2017		Petrů		Blatt/Sheet 1/1													



Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.