

Rack Mount Power Distribution Unit

01230401



Rack Mount Power Distribution Unit: 3 Phase 400VAC, IEC30309 32A 3P+N+E plug input, 18 ways C13 + 6 ways C19 output. With 3× 32A Air Circuit Breaker & Digital Amps / Volts Meter.

PRODUCT LABEL

Product Name	Designated Power Distribution Unit for Cabinet
Item Code	01230401 (Model: AUE2211H1-24AVKTVB-1806)
Rating Voltage	400 VAC 50/60 Hz
Rating Current	3× 32A
Max. Power	3× 8000 W
Safety Authentication	CE, RoHS

Technical Specifications

ITEM	DESCRIPTION
Socket Type	[6× IEC320 C19 Socket] + [18× IEC320 C13 Socket]
Socket Quantity	24 way
Power Input	Left end single input (Bottom feed power input)
Bracket Install	Inverse installation (OU)
Cable with Plug	IEC60309 plug (32A 3P + N + E)
Control Function	3× 32A Air Circuit Breaker
Protection Function	3-phase digital Amps / Volt Meter [1]
Case	Black
Cable Specifications	5 × 6.0 mm ² × 3M
Product Size (L×W×H mm)	1638 × 56 × 44.4
Mounting Length	1617 mm
Case Length	1585 mm
Fittings	2 pcs Ø6 × 16mm cross bolt, 2 pcs M6 float nut, 2 pcs removable brackets, 8pcs M3-6 fast pan screws
Interior Connection wire	2.5 mm ² (14AWG)
Interior Connection style	Group connection
Fix the cable	Cable clamp (21)

Product Image



IEC60309 plug (32A 3P+N+E)

VertivCo.com

© 2019 Vertiv Co. All rights reserved. Vertiv, the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

Rack Mount Power Distribution Unit (01230401)-DS-EN / 022619