



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.


FRONT VIEW



REAR VIEW



UPPER VIEW



RoHS COMPLIANT

OUTPUT POWER

| BANK | PHASE | RECEPTACLE TYPE (QUANTITY) | VOLTAGE (V) | MAX. CONTINUOUS AMPS (A) | |
|------|-------|----------------------------|-------------|--------------------------|----------|
| | | | | PER RECEPTACLE | PER BANK |
| A | L1 | 6xC13, 2xC19 | 100-240 | 10/16 | 16 |

| METERING PARAMETER | MEASUREMENT ACCURACY |
|--------------------|---|
| VOLTAGE | ±1 % + 0.1 VAC |
| CURRENT | ±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING |

INPUT POWER

| INPUT CORD | INPUT SOCKET | WIRE COUNT | FREQUENCY (Hz) | VOLTAGE (V) | RATED AMPS (A) | MAX. CONT. AMPS (A) |
|------------|---------------|--------------|----------------|-------------|----------------|---------------------|
| - | IEC 60320 C20 | 1/N/PE, 2/PE | 50/60 | 100-240 | 16 | 16 |

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CE-mark: LVD, EMC, RoHS (incl. harmonized standards hereunder)
- CB certification: IEC 60950-1 (2nd)
- BG certification: BV-BG (factory inspected)
- WEEE COMPLIANT
- "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H2I)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

1. UNIT DIMENSIONS: 440 mm (17.3") W x 250 mm (9.8") D x 44 mm (1.7") H
2. UNIT WEIGHT: 5.3 kg / 11.7 lbs
3. SHIPPING DIMENSIONS: 543 mm (21.4") W x 410 mm (16.1") D x 165 mm (6.5") H
4. SHIPPING WEIGHT: 5.9 kg / 13 lbs
5. (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. BOTH SIDES CAN BE USED TO MOUNT THE PDU.

| | | | | | | | | | |
|---|--|---|--|----------------------|--|--|--|-----------------------|--|
| <p>Dimensions in mm</p> | | Allgemeintoleranzen General tolerances | | Oberfläche Finish | | Werkstoff / Material | | Gewicht: Weight: - | |
| | | - | | - | | - | | - | |
| | | Date | | Name | | Bezeichnung / Description MPH2-ECC_C20-16A_6N-20 Input and Branch Metered + Outlet Switched | | | |
| | | 20/05/16 | | Racek | | | | | |
| | | 20/05/16 | | Votýpka | | | | | |
| | | Approved | | - | | - | | - | |
| | | | | | | Zeichnungs-Nr. / Drawing no. | | Maßstab Scale | |
| | | | | | | MPHC2441 | | 1:5 | |
| | | | | | | Verwendet in / Used in | | Blatt/Sheet | |
| | | | | | | - | | 1/1 | |
| Rev. Change Date Name B 18154 13.06.2017 Petrú | | | | | | | | | |
| | | | | | | | | | |