



Disclose and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugelassen. Alle Rechte vorbehalten.



OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	1xC13, 2xC19	200-240	12/16	16
B	L2-L3	1xC13, 2xC19	200-240	12/16	16
C	L3-L1	1xC13, 2xC19	200-240	12/16	16
D	L1-L2	1xC13, 2xC19	200-240	12/16	16
E	L2-L3	1xC13, 2xC19	200-240	12/16	16
F	L3-L1	1xC13, 2xC19	200-240	12/16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
-	-	3/PE	50/60	200-240	60	48

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

AGENCY COMPLIANCE:
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
 - FCC certification
 - CB certification: IEC 60950-1 (2nd)
 - "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H22)

ENVIRONMENTAL RATING:
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:**
 1. UNIT DIMENSIONS: 1826.5 mm (75.0") H x 50 mm (2.0") D x 56 mm (2.2") W
 2. UNIT WEIGHT: 4 kg / 8.8 lbs
 3. SHIPPING DIMENSIONS: 2017.0 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
 4. SHIPPING WEIGHT: 6,8 kg / 15 lbs
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

	Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -
	-		-		-		-
Date		Name		Bezeichnung / Description			
11/07/16		Racek		MPH2-NRV_3P4W-60A_6N-120_HW			
11/07/16		Votýpka		Input and Branch Metered + Outlet Metered/Switched			
-		-		Zeichnungs-Nr. / Drawing no.			
-		-		MPHR1356			
-		-		Verwendet in / Used in			
-		-		Maßstab Scale			
-		-		1:5			
-		-		Blatt/Sheet			
-		-		1/1			

Rev.	Change	Date	Name
A	18131	31.05.2017	Petrú

