



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



REAR VIEW



SIDE VIEW



FRONT VIEW



NEMA L5-20P
(20 A, 1/N/PE, 100-120 V)

L5-20P

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)
- "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H22)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

1. UNIT DIMENSIONS: 916.5 mm (36.1") H x 50 mm (2.0") D x 56 mm (2.2") W
2. UNIT WEIGHT: 2.3 kg / 5.0 lbs
3. SHIPPING DIMENSIONS: 1197 mm (47.1") H x 218 mm (8.6") D x 137 mm (5.4") W
4. SHIPPING WEIGHT: 4.3 kg / 9.5 lbs
5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

OUTPUT POWER

BANK	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BANK
A	L1	18xNEMA 5-20	100-120	16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	L5-20P	1/N/PE	50/60	100-120	20	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

<p>Dimensions in mm</p>	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
	Drawn	13/01/16	Name	Bezeichnung / Description	
	Checked	13/01/16	Blass	MPH2-NBV_L5-20P_18A	
	Approved	-	Votýpka	Input and Branch Metered	
	<p>VERTIV™</p>			Zeichnungs-Nr. / Drawing no.	Maßstab Scale
				MPHB3303	
Rev.	Change	Date	Name	Verwendet in / Used in	Blatt/Sheet
C	18131	05.06.2017	Petrů	-	1/1