


Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



NEMA L21-30P
(30 A, 3/N/PE, 100-120/173-208 V)

OUTPUT POWER **NEMA L21-30P**

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1	3xNEMA 5-20	100-120	16	16
B	L2	3xNEMA 5-20	100-120	16	16
C	L3	3xNEMA 5-20	100-120	16	16
D	L1	3xNEMA 5-20	100-120	16	16
E	L2	3xNEMA 5-20	100-120	16	16
F	L3	3xNEMA 5-20	100-120	16	16

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- CE-mark: LVD, EMC, RoHS (incl. harmonized standards hereunder)
- CB certification: IEC 60950-1 (2nd)
- BG certification: BV-BG (factory inspected)
- WEEE COMPLAINT

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W
2. UNIT WEIGHT: 4 kg/8.8 lbs
3. SHIPPING DIMENSIONS: 2017 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
4. SHIPPING WEIGHT: 6.81 kg/15 lbs
5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

INPUT POWER

INPUT CORD	INPUT SOCKET	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 Ft / 3m	NEMA L21- 30P	3/N/PE	50/60	100-120/173-208	30	24

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

<p>Dimensions in mm</p>	Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -
	-		-		-		-
Date		Name		Bezeichnung / Description			
10/12/15		Blass		MPH2-NRV_L21-30P_18A			
10/12/15		Votýpka		Input and Branch Metered + Outlet Metered/Switched			
-		-		Zeichnungs-Nr. / Drawing no.			
-		-		MPHR1423			
-		-		Verwendet in / Used in			
-		-		-			
Rev.	Change	Date	Name	Maßstab Scale			
C	18131	31.05.2017	Petrú	1:5			
				Blatt/Sheet			
				1/1			