



NetSure™

Dc Power System
for Telecom Power

NetSure™ 211B4

NetSure™ 211D4



NetSure™ 211B4 is an optimized solution for telecom applications designed for the efficient performance, unmatched features and competitive cost. Array of features aid remote monitoring and low voltage battery disconnect. The system comes fully equipped with integrated AC and DC distribution.

FEATURES

- Provides up to 40 A at 48V in one cabinet
- User configurable 5 relay contacts
- Multiple Rectifier Fail Alarm
- Operates with global AC voltages
- Designed to operate in poor power quality environments
- Easy for Installation & True Front access for maintenance
- Cabinets equipped with DC distribution
- Low voltage battery disconnection to protect batteries
- Utilizes 48V 1000W rectifier



APPLICATIONS

- NetSure™ is ideal for use in central office, BIS, and small Telecom loads, server racks, small telecom loads, micro BTS, EPABX, BroadBand and IPV
- The DC power system works in both centralized and distributed architecture plant layouts and is suitable for any -48VDC application with 1 Phase.
- Due to the weight distribution of the NetSure, an entire DC power plant can be installed in a raised floor environment, subject to Floor loading limitations or mounted on the Battery
- Ideal for Smart City application

System Code	211B4
Ampere (A) @ 48V	40
Wattage (W)	2000
Max. Number of Rectifier	2
Rectifier Type	R48-1000
Controller	M522S/M530S/530B
Dimension W x D x H in (mm)	483 X 370 X 45
Net Weight with Rectifier (kg)	20

NetSure™ 211D4 is an optimized solution for telecom applications designed for the efficient performance, unmatched features and competitive cost. Array of features aid remote monitoring and low voltage battery disconnect. The system comes fully equipped with integrated AC and DC distribution.

FEATURES

- Provides up to 80 A at 48V in one cabinet
- User configurable 5 relay contacts
- Multiple Rectifier Fail Alarm
- Operates with global AC voltages
- Designed to operate in poor power quality environments
- Easy for Installation & True Front access for maintenance
- Cabinets equipped with DC distribution
- Low voltage battery disconnection to protect batteries
- Utilizes 48V 1000W rectifier



APPLICATIONS

- NetSure™ is ideal for use in central office, BIS, and small Telecom loads, server racks, small telecom loads, micro BTS, EPABX, Broad band and IPV.
- The DC power system works in both centralized and distributed architecture plant layouts and is suitable for any -48VDC application with 1 Phase AC supply.
- Due to the weight distribution of the NetSure, an entire DC power plant can be installed in a raised floor environment, subject to Floor loading limitations or mounted on the Battery.



System Code	211D4
Ampere (A) @ 48V	80
Wattage (W)	4000
Max. Number of Rectifier	4
Rectifier Type	R48-1000
Controller	M522S/M530S/530B
Dimension W x D x H in (mm)	450 x 370 x 186
Net Weight with Rectifier (kg)	30



VertivCo.com | E-mail : marketing.india@vertivco.com | Toll free : 1-800-2096070

Vertiv Energy Private Limited | Plot C-20, Rd No.19, Wagle Ind Estate, Thane (W), 400604. India

© 2017 Vertiv Co. All rights reserved.